

Inhaltsverzeichnis

Suchen über Klassifizierung im AWC 3

Suchen über Klassifizierung im AWC

The screenshot displays the Siemens Teamcenter AWC (Advanced Workcenter) interface. The top navigation bar includes the 'Teamcenter' logo, a search bar with filters for 'Beliebige Eigenschaft' and 'Beliebige Kategorie', and the 'SIEMENS' logo. Below the navigation bar, the main dashboard is organized into several functional tiles:

- AKTIVE AUFGABEN:** Shows task counts for 'Neu', 'Gesamt', and 'Überfällig' (0/0/0).
- ORDNER:** A folder icon representing a directory structure.
- TEAMCENTER DOCUMENTATION:** A tile with a question mark icon.
- HILFE:** A tile with a question mark icon.
- AUSDRUCKE:** A tile with a printer icon.
- GESPEICHT. SUCHEN:** A tile with a magnifying glass icon.
- ABONNEMENT:** A tile with a Wi-Fi signal icon.
- BERICHTE:** A tile with a document and bar chart icon.
- CLASSIFICATION:** A tile with a hierarchical tree icon, highlighted with a green border.
- FAVORITEN:** A tile with a star icon.
- MEINE DATEN:** A tile with a magnifying glass icon.
- FRAGEN:** A tile with a speech bubble and question mark icon.
- ASSIGNMENT LISTS:** A tile with an icon showing a hierarchy and people.

The interface also features a left sidebar with navigation icons and a bottom status bar with system icons and a user profile picture.

The screenshot displays the Siemens AWC (Advanced Work Center) interface for classification. On the left, a navigation pane titled 'Navigieren' shows a hierarchical tree of classes. The '27-26-01 Resistance' class is highlighted with a green box. A green arrow points from this box to a search bar at the bottom of the navigation pane labeled 'Suchen'. The main area on the right shows a grid of component cards, each with a title and a small schematic diagram. The cards are: '27-26-01-02 Resistor, linear', '27-26-01-03 Varistor', '27-26-01-04 Positive Temperature ...', '27-26-01-05 Negative Temperature...', '27-26-01-06 Fusing resistor', and '27-26-01-07 Potentiometer'. The breadcrumb path at the top of the main area reads: 'ecl@ss > 27 Electric engineering, automation, process control engineering > 27-26 Component (electronic) > 27-26-01 Resistance'.

Klassifizierung SIEMENS

349 Ergebnisse wurden für "27-26-01 Resistance" gefunden

Navigieren

Klassen Filters

VERFEINERN

Automatisch aktualisieren:

[Alle löschen](#)

Nach Eigenschaft filtern

Letzter ändernder Benutzer

- Stefan Laquai (s.laquai)(221)
- m.avis (m.avis)(104)
- Ulrich Ockelmann (u.ockelmann)(22)
- infodba (infodba)(2)

Eigentümer

- e.avis (e.avis)(339)
- Ulrich Ockelmann (u.ockelmann)(9)
- Christian Hetmanek (c.hetmanek)(1)

Freigabedatum

DD.MM.YYYY - DD.MM.YYYY

- 2019(325)
- 2020(24)

Freigabestatus

- Av4_Freigegeben(335)
- Av4_Inactive(14)

Änderungsdatum

[Alle anwenden](#)

	RES LIN 390R 1% 1W 010553391 Revision: 001
	RES LIN 681R 1% 1W 010553681 Revision: 001
	RES LIN 50R 0.05% 0.4W 000710490 Revision: 001
	RES LIN 250R 0.05% 0.25W 000710251 Revision: 001
	RES LIN 10k 1% 0.25W 490000125 Revision: 001
	RES LIN 1k 0.1% 0.2W 490000452 Revision: 001
	RES LIN 120R 1% 0.063W 490010077 Revision: 002
	RES LIN 24k 1% 0.25W 490000134 Revision: 001
	RES LIN 2k7 1% 0.25W 490000110 Revision: 001
	RES LIN 20k 0.1% 0.25W 490000418 Revision: 001

The screenshot shows the Siemens AWC interface for classification. The main window is titled 'Klassifizierung' and displays 335 results for the search '27-26-01 Resistance'. A sidebar on the left, titled 'Navigieren', contains a 'Filtern' section with the following settings:

- VERFEINERN**
- Automatisch aktualisieren:
- Freigabestatus: Av4_Freigegeben
- Nach Eigenschaft filtern: [Empty text box]
- Freigabestatus**
 - Av4_Freigegeben(335)
 - Av4_Inactive(14)
- Letzter ändernder Benutzer**
 - Stefan Laquai (s.laquai)(221)
 - m.avis (m.avis)(104)
 - Ulrich Ockelmann (u.ockelmann)(8)
 - infodba (infodba)(2)
- Eigentümer**
 - e.avis (e.avis)(325)
 - Ulrich Ockelmann (u.ockelmann)(9)
 - Christian Hetmanek (c.hetmanek)(1)
- Freigabedatum**
 - 2019(325)

At the bottom of the sidebar, there is a green button labeled 'Alle anwenden'. A green arrow points from this button to the 'Av4_Freigegeben(335)' filter option. Another green arrow points from the 'Av4_Freigegeben(335)' option to a list of results on the right. A green box labeled 'Gefiltertes Ergebnis' is positioned over the first few items in the results list.

The results list contains the following items:

- RES LIN 390R 1% 1W (010553391) Revisions: 001
- RES LIN 681R 1% 1W (010553681) Revisions: 001
- RES LIN 50R 0.05% 0.4W (000710490) Revisions: 001
- RES LIN 250R 0.05% 0.25W (000710251) Revisions: 001
- RES LIN 10k 1% 0.25W (490000125) Revisions: 001
- RES LIN 1k 0.1% 0.2W (490000452) Revisions: 001
- RES LIN 120R 1% 0.063W (490010077) Revisions: 002
- RES LIN 24k 1% 0.25W (490000134) Revisions: 001
- RES LIN 2k7 1% 0.25W (490000110) Revisions: 001
- RES LIN 20k 0.1% 0.25W (490000418) Revisions: 001